
# High Power 3 µm DPSSL Modules



- · Compact monolithic laser systems
- · Highly efficient diode pumping
- · Fiber-coupled versions available
- · No high-voltage required
- · Reduced waste heat
- · Maintenance free
- · Process variability



## **Specifications**

	DPM-2 (Er:YAG) free / fiber [1]	DPM-25 (Er:YAG) free / fiber [1]	DPM-50 (Er:YAG) free / fiber [1]
Optical Parameters			
<ul> <li>Wavelength</li> <li>Average Output Power (max)</li> <li>Pulse Energy (max)</li> <li>Pulse Repetition Rate</li> <li>Pulse Duration</li> <li>Average Current (max)</li> <li>Mode of Operation</li> <li>Efficiency (optical-optical)</li> <li>Beam Shape (focus)</li> <li>Free Beam Quality</li> <li>Free Beam Diameter</li> <li>Free Divergence (half angle)</li> </ul>	2940 nm 2 / 1.2 W 20 <sup>[2]</sup> / 13 <sup>[2]</sup> mJ up to 1 kHz [40 - 1000 <sup>[3]</sup> ] μs 30 A Pulsed > 10 % Top Hat like M <sup>2</sup> < 5 0.6 mm < 25 mrad	2940 nm 25 / 16 W 300 <sup>[2]</sup> / 200 <sup>[2]</sup> mJ up to 1 kHz (40 - 1000 <sup>[3]</sup> ) μs 25 A Pulsed > 10 % Top Hat like M <sup>2</sup> < 30 1.6 mm < 25 mrad	2940 nm 50 / 33 W 600 <sup>(2)</sup> / 400 <sup>(2)</sup> mJ up to 1 kHz (40 - 1000 <sup>(3)</sup> ) μs 25 A Pulsed > 10 % Top Hat like M <sup>2</sup> < 30 1.6 mm < 50 mrad
• Fiber Diameter GeO <sub>2</sub> (1)	~ 250 µm (NA < 0.2)	~ 250 µm (NA < 0.2)	~ 450 µm (NA < 0.2)
Cooling Requirements	- 200 μπ (ΝΑΝ 0.2)	230 μπ (ΝΑΝ 0.2)	400 μπ (ΝΑ ( 0.2)
· Coolant Temperature	Air-cooled or cooled with distilled Water with Algaecide and Corrosion Inhibitor (20 - 35) °C	Distilled Water with Algaecide and Corrosion Inhibitor (20 - 25) °C	Distilled Water with Algaecide and Corrosion Inhibitor (20 - 25) °C
· Coolant Flow Rate	≥ 1 lpm	> 5 lpm	≥ 6 lpm
· Coolant Pressure	(1 - 3) bar	(2 - 5) bar	(3 - 5) bar
· Required Cooling Power	~ 150 W @ 25 °C Environment Temperature	≥ 540 W @ 25 °C Environment Temperature	≥ 780 W @ 25 °C Environment Temperature
Electrical Parameters			
<ul><li>Diode Forward Voltage</li><li>Diode Forward Current (max)</li><li>Average Power Consumption</li></ul>		~ 20 V 300 A Pulsed < 450 W	~ 30 V 300 A Pulsed < 900 W
Mechanical Dimensions			
<ul><li>Dimension (L x W x H)</li><li>Weight</li><li>Emission Height</li></ul>	(29 x 38 x 22) mm <sup>3 (4)</sup> 80 g -	(59 x 78 x 59) mm <sup>3 (4)</sup> 1 kg 38.1 mm	(90 x 78 x 59) mm <sup>3 (4)</sup> 1 kg 38.1 mm

<sup>[1]</sup> Fiber as specified by Pantec

 $<sup>^{\</sup>text{(2)}}$  For pulse durations > 600  $\mu s$ 

 $<sup>^{\</sup>text{\tiny{[3]}}}$  600  $\mu s$  standard, 1000  $\mu s$  on request

<sup>(4)</sup> Dimensions for bare modules



#### Laser Diode Drivers

The LDD series are economic QCW laser diode driver modules designed to provide high current pulses to drive 3m.i.k.r.o.n.™ laser modules in various applications. The drivers deliver output currents up to 300 A and pulse widths variable from 50 µs up to 1000 µs operation [3]. Up to 1000 W average output power is available with the supplied heatsink. Several safety features are integrated to protect both laser module and laser driver.

	DPM-2 (Er:YAG) / DPM-25 (Er:YAG)	DPM-50 (Er:YAG)	
Laser Diode Driver	LDD-20300	LDD-30300	
· Output Current	up to 300 A	up to 300 A	
· Rise Time (10 - 90%)	< 20 µs	< 20 μs	
<ul> <li>Mechanical Dimensions (W x D x H)</li> </ul>	(195 x 140 x 110) mm <sup>3</sup>	(195 x 140 x 130) mm <sup>3</sup>	
<ul> <li>Additional Features</li> </ul>	Safety circuit and	Safety circuit and	
	communication interface	communication interface	

 $<sup>^{(3)}</sup>$  600  $\mu$ s standard, 1000  $\mu$ s on request (different mechanical dimensions)

#### Test and Evaluate



The 3m.i.k.r.o.n.<sup>TM</sup> evalution kits are ready-to-use and straightforward laboratory systems for first feasibility studies in research environment. The evaluation kits are available with different kinds of laser sources (see front page), shortens the development time, enables flexibility and a fast demonstration of feasibility. The test systems are delivered with your requested laser source, a laser control system and a cooling system for laboratory use only.

Please contact us for more information on rental or purchase conditions: info@pantec-biosolutions.com

### 3m.i.k.r.o.n.™ Applications

Medical	Industrial
<ul> <li>Aesthetics / Dermatology</li> </ul>	<ul> <li>Material Processing (Drilling, Cutting, Melting, Welding, Evaporation)</li> </ul>
· Dentistry	· Analytics
· ENT	· Security
· Lithotripsy	· Defense
· Minimally-Invasive Surgery	
· Orthopedics	
· otc	

#### More Services



Customized laser sources
Optical and mechanical design
Contract development and manufacturing
Medical device consulting (IP research, Medical CE, ...)



